

Model ED 720 | Drying and heating chambers with natural convection

The strengths of a BINDER ED series drying chamber include routine drying and sterilization tasks up to 300 °C. Thanks to the natural convection, all thermal processes which use this drying chamber are highly efficient. The ED series ensures fast, uniform drying.

BENEFITS

- · Best energy efficiency on the market
- · Excellent temporal and spatial temperature accuracy
- · USB connection for recording data
- Temperature range up to +300 °C



Model 720

MAIN FEATURES

- Temperature range: +5 °C above ambient temperature to +300 °C
- Up to 30% lower energy consumption compared to conventional units on the market
- High temperature accuracy thanks to APT.line™ technology
- Natural convection
- Controller with LCD display
- · Electromechanical control of the exhaust air flap

- 2 chrome-plated racks
- Class 2 integrated independent adjustable temperature safety device (DIN 12880) with visual alarm
- Ergonomic handle design
- USB port for recording data

ORDERING INFORMATION

Interior volume [L]	Voltage	Option model	Version	ArtNo.
743	400 V 3~ ph 50/60 Hz	Standard	ED720-400V	9010-0341




TECHNICAL DATA

Description	ED720-400V ¹
Article Number	9010-0341
Performance Data Temperature	
Temperature range +5 °C above ambient temperature to [°C]	300
Temperature variation at 150 °C [± K]	3.2
Temperature fluctuation at 150 °C [± K]	0.8
Heating-up time to 150 °C [min]	85
Recovery time after 30 seconds door open at 150 °C [min]	25
Electrical data	
Rated Voltage [V]	400
Power frequency [Hz]	50/60
Nominal power [kW]	4.1
Unit fuse [A]	16
Phase (Nominal voltage)	3~
Measures	
Interior volume [L]	743
Net weight of the unit (empty) [kg]	161
Permitted load [kg]	315
Load per rack [kg]	45
Wall clearance back [mm]	160
Wall clearance sidewise [mm]	100
Internal Dimensions	
Width [mm]	960
Height [mm]	1280
Depth [mm]	605
Doors	
Inner doors	2
Unit doors	2
Housing dimensions not incl. fittings and connections	
Width net [mm]	1165
Height net [mm]	1590
Depth net [mm]	870
Environment-specific data	
Energy consumption at 150 °C [Wh/h]	700
Fixtures	
Number of shelves (std./max.)	2/16

¹ All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10%. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.



DIMENSIONS incl. fittings and connections [mm]



OPTIONS

Designation	Description	*	ArtNo.
	back		
	10 mm	01	8012-1282
	30 mm	01	8012-0540
	50 mm	01	8012-0546
	left		
	10 mm	01	8012-1275
	30 mm	01	8012-1018
	50 mm	01	8012-1022
	100 mm	01	8012-1030
-	right		
Aug	10 mm	01	8012-1268
	30 mm	01	8012-1017
	50 mm	01	8012-1021
	100 mm	01	8012-1031
	top		
	10 mm	01	8012-1262
	30 mm	01	8012-0539
	50 mm	01	8012-054
	100 mm	01	8012-102
	Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device	-	8012-1635
Analog output 4-20 mA	for temperature values (output not adjustable)	02	8012-1623
	for temperature; for extending the measurement in center of chamber to include another test temperature	-	8012-1115
expanded	for temperature, measurement in center of chamber at specified temperature	-	8012-1134
Calibration certificate,	temperature measurement incl. certificate and 27 measuring points at specified temperature	-	8012-1593
Access port with silicone plug Alarm function for overheating Analog output 4-20 mA Calibration certificate, expanded Calibration certificate, temperature Class 3.1 independent temperature safety device Clock Door gasket Door lock Ethernet interface Inner chamber, reinforced	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	-	8012-1572
	temperature measurement incl. certificate, 9 measuring points at specified temperature	-	8012-1551
emperature safety	with visual alarm (DIN 12880)	-	8012-098
Clock	battery-backed	-	8012-1640
Door gasket	made of FKM, silicone-free		8012-1013
Door lock	lockable door handle	-	8012-1817
Ethernet interface	for Multi Management Software APT-COM™	-	8012-1836
	max. total load 350 kg	-	8012-1827
	with two 15 W light bulbs		
nterior lighting	400 V option model	_	8012-1824
* Notes > See last page			80

^{*} Notes > See last page



Designation	Description	*	ArtNo.
Measurement of air exchange rate	in accordance with ASTM D5374, definition and protocol according to ambient temperature	-	8012-0195
Pt 100 temperature sensor	additional flexible Pt 100, interior, for displaying the temperature on the unit display	-	8012-1619
Viewing window and	viewing window (triple insulating glass) in door, 300 x 480 mm, and 30 W interior		
interior lighting	400 V option model	-	8012-1830
* Notes , See last nage			

^{*} Notes > See last page

ACCESSORIES

Designation	Description	*	ArtNo.
APT-COM™ 4 BASIC-	for simple logging and documentation requirements with up to 5 networked units.		
Edition	version 4, BASIC edition	-	9053-003
APT-COM™ 4 GLP-	for working under GLP-compliant conditions. Measured values are documented in a tamper-proof way in line with the requirements of FDA Regulation 21 CFR 11.		
Edition	version 4, GLP edition	-	9053-004
APT-COM™ 4 PROFESSIONAL-Edition	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.		
	version 4, PROFESSIONAL edition	-	9053-004
Data Logger Kit	T 350: For continuous temperature logging from 0 °C to 350 °C; kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit	-	8012-071
Data Logger Software	LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)	-	8012-082
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-001
	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit		
	Digital in PDF format	-	7057-000
Ovelification desuments	Hard copy inside folder	-	7007-000
Qualification documents	$IQ/OQ/PQ$ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ ; parameters: temperature, CO_2 , O_2 – or pressure, depending on unit		
	Digital in PDF format	-	7057-000
	Hard copy inside folder	-	7007-000
a a l	chrome plated	-	6004-017
Rack	stainless steel	-	6004-016
Rack, heavy load	Stainless steel, max. load per rack 70 kg	-	6004-024

^{*} Notes > See last page

SERVICES

Designation	Description	*	ArtNo.
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	05	DL10-0100
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0500
Maintenance contracts			
Maintenance services			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	05	DL20-0710
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one test temperature specified by the user in the center of the usable space, including certificate	05	DL20-0910

^{*} Notes > See last page



Description	*	ArtNo.
One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	05	DL20-0200
Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	05	DL20-0810
Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	03, 04, 05	DL30-0101
Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	03, 04, 05	DL30-0102
including certificate (in accordance with ASTM D5374)	03, 04, 05	DL33-000
Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0118
Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-012;
Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	03, 04, 05	DL30-0109
Execution of IQ/OQ in accordance with qualification folder	05	DL40-0100
Execution of IQ/OQ/PQ in accordance with qualification folder	05	DL44-0500
The warranty is extended by 1 year from the delivery date, wear parts are excluded	_	DL50-001
	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate Calibration of one (1) test temperature specified by the user in center of chamber, including certificate Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate including certificate (in accordance with ASTM D5374) Temperature measurement with 18 measuring points with a set value specified by the user, including certificate Temperature measurement with 27 measuring points with a set value specified by the user, including certificate Temperature measurement with 9 measuring points with a set value specified by the user, including certificate Execution of IQ/OQ in accordance with qualification folder Execution of IQ/OQ in accordance with qualification folder	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate Calibration of one (1) test temperature specified by the user in center of chamber, including certificate Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate including certificate (in accordance with ASTM D5374) Temperature measurement with 18 measuring points with a set value specified by the user, including certificate Temperature measurement with 27 measuring points with a set value specified by the user, including certificate Temperature measurement with 9 measuring points with a set value specified by the user, including certificate Execution of IQ/OQ in accordance with qualification folder Execution of IQ/OQ/PQ in accordance with qualification folder Execution of IQ/OQ/PQ in accordance with qualification folder Execution of IQ/OQ/PQ in accordance with qualification folder

^{*} Notes > See last page



NOTES

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. UL mark is not granted when this option is used.
- 02
- Sensor calibration is performed in an accredited calibration laboratory. 03
- Calibration is performed according to the BINDER factory standard.
- Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

BINDER GmbH

Tuttlingen, Germany TEL +49 7462 2005 0 FAX +49 7462 2005 100 info@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 FAX +852 39070507 asia@binder-world.com www.binder-world.com

BINDER Environmental Testing Equipment (Shanghai) Co., Ltd. Shanghai, P.R. China TEL +86 21 685 808 25 FAX +86 21 685 808 29 china@binder-world.com www.binder-world.com

Representative Office for CIS

Moscow, Russia TEL +7 495 988 15 16 FAX +7 495 988 15 17 russia@binder-world.com www.binder-world.com

BINDER Inc. Bohemia, NY, USA TEL +1 631 224 4340 FAX +1 631 224 4354

usa@binder-world.com www.binder-world.us