



Peltier-cooled incubator IPP55plus

Microbiology, zoology, food, cosmetics or pharma industry: the energy-saving cooled incubator with Peltier elements heats up and cools down seamlessly in one system.



With the help of our model selection, with dimensioned model sketches and extensive technical data for download, you will find your perfect Peltier-cooled incubator. For large volumes in conjunction with rapid temperature changes, the Memmert compressor-cooled incubator is recommended. Flexibility and technical features of our appliances meet all possible needs. Put us to the test!





Setting accuracy temperature range Setting accuracy temperature 2 Pt100 sensors Class A in 4-wire-circuit, mutually monitoring and taking over the performance at the same temperature value Control technology ControlCOCKPIT TwinDISPLAY. Adaptive multifunctional digital PID-microprocessor controller with 2 high-definition TFT-colour displays. Language setting German, English, Spanish, French, Polish, Czech, Hungarian Timer Digital backwards counter with target time setting, adjustable from 1 minute to 99 days Function SetpointWAIT the process time does not start until the set temperature is reached Calibration three freely selectable temperature values adjustable parameters temperature (Celsius or Fahrenheit), programme time, time zones, summerlime/wintertime Ventilation Convection forced ventilation by Peltier fan Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethemet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a present tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row Peltier energy-saving Peltier heating-focoling system integrated in the rear (heat pump principle)	Temperature	
Temperature 2 P1100 sensors Class A in 4-wire-circuit, mutually monitoring and taking over the performance at the same temperature value Control technology ControlCCKPIT TwinDISPLAY, Adaptive multifunctional digital PID-microprocessor controller with 2 high-definition TFT-colour displays. Language setting German, English, Spanish, French, Polish, Czech, Hungarian Timer Digital backwards counter with target time setting, adjustable from 1 minute to 99 days Function SetpointWAIT the process time does not start until the set temperature is reached Calibration three freely selectable temperature values adjustable parameters temperature (Celsius or Fahrenheit), programme time, time zones, summertime/wintertime Ventilation Convection forced ventilation by Peltier fan Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethemet interface or USB port Safety Temperature control over- and undertemperature protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the septoint value at a preset telenace range, alarm in case of over- or undertemperature, healing function is switched off in case of overtemperature, cooling function in case of undertemperature. Autodiagnostic system Alarm Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Working temperature range	from 0°C to +70°C
Control technology ControlCOCKPIT TwinDISPLAY. Adaptive multifunctional digital PID-microprocessor controller with 2 high-definition TFT-colour displays. Language setting German, English, Spanish, French, Polish, Czech, Hungarian Timer Digital backwards counter with target time setting, adjustable from 1 minute to 99 days Function SetpointWAIT the process time does not start until the set temperature is reached Calibration three freely selectable temperature values adjustable parameters temperature (Celsius or Fahrenheit), programme time, time zones, summertime/wintertime Ventilation Convection forced ventilation by Peltier fan Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	-	0.1°C
TwinDISPLAY. Adaptive multifunctional digital PID-microprocessor controller with 2 high-definition TFT-colour displays. Language setting German, English, Spanish, French, Polish, Czech, Hungarian Digital backwards counter with target time setting, adjustable from 1 minute to 99 days Function SetpointWAIT the process time does not start until the set temperature is reached Calibration three freely selectable temperature values adjustable parameters temperature (Celsius or Fahrenheit), programme time, time zones, summertime/wintertime Ventilation Convection forced ventilation by Peltier fan Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Pettier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Temperature	
TFT-colour displays. Language setting German, English, Spanish, French, Polish, Czech, Hungarian Timer Digital backwards counter with target time setting, adjustable from 1 minute to 99 days Function SetpointWAIT the process time does not start until the set temperature is reached Calibration three freely selectable temperature values adjustable parameters temperature (Celsius or Fahrenheit), programme time, time zones, summertime/wintertime Ventilation Convection forced ventilation by Peltier fan Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature. Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Control technology	
Timer Digital backwards counter with target time setting, adjustable from 1 minute to 99 days Function SetpointWAIT the process time does not start until the set temperature is reached Calibration three freely selectable temperature values adjustable parameters temperature (Celsius or Fahrenheit), programme time, time zones, summertime/wintertime Ventilation Convection forced ventilation by Peltier fan Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	ControlCOCKPIT	· · · · · · · · · · · · · · · · · · ·
Function SetpointWAIT the process time does not start until the set temperature is reached Calibration three freely selectable temperature values adjustable parameters temperature (Celsius or Fahrenheit), programme time, time zones, summertime/wintertime Ventilation Convection forced ventilation by Peltier fan Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature. Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Language setting	German, English, Spanish, French, Polish, Czech, Hungarian
Calibration three freely selectable temperature values adjustable parameters temperature (Celsius or Fahrenheit), programme time, time zones, summertime/wintertime Ventilation Convection forced ventilation by Peltier fan Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Timer	Digital backwards counter with target time setting, adjustable from 1 minute to 99 days
temperature (Celsius or Fahrenheit), programme time, time zones, summertime/wintertime Ventilation Convection forced ventilation by Peltier fan Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Function SetpointWAIT	the process time does not start until the set temperature is reached
Ventilation Convection forced ventilation by Peltier fan Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature. Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Calibration	three freely selectable temperature values
Communication Documentation programme stored in case of power failure Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature. heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	adjustable parameters	temperature (Celsius or Fahrenheit), programme time, time zones, summertime/wintertime
Programming AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row		forced ventilation by Peltier fan
AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Communication	
Safety Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Documentation	programme stored in case of power failure
Temperature control over- and undertemperature monitor TWW, protection class 3.3 or adjustable temperature limiter TWB, protection class 2, selectable on display AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Programming	
AutoSAFETY additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Safety	
setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature Autodiagnostic system for fault analysis Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Temperature control	
Alarm visual and acoustic Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	AutoSAFETY	setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating
Heating concept Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Autodiagnostic system	for fault analysis
Peltier Heating and cooling performance distribution by individual control of the Peltier elements in the upper and lower row	Alarm	visual and acoustic
and lower row	Heating concept	
Peltier energy-saving Peltier heating-/cooling system integrated in the rear (heat pump principle)	Peltier	,
	Peltier	energy-saving Peltier heating-/cooling system integrated in the rear (heat pump principle)

Standard equipment

Scope of delivery	incl. works calibration certificate for +10°C and +37°C
Door	fully insulated stainless steel door with2-point locking (compression door lock)
Door	inner glass door
Internals	1 stainless steel grid

Stainless steel interior

Volume	53 I
Dimensions W x H x D in mm	w _(A) x h _(B) x d _(C) : 400 x 400 x 330 mm
Max. number of internals	4
Max. loading of chamber	80 kg
Max. loading per internal	20 kg

Textured stainless steel casing

Dimensions	w _(D) x h _(E) x d _(F) : 585 x 784 x 604 mm
Housing	rear zinc-plated steel

Electrical data

Voltage	230 V, 50/60 Hz
Electrical load	approx. 275 W
Voltage	115 V, 50/60 Hz
Electrical load	approx. 275 W

Packing/shipping data

the appliances must be transported upright

Customs tariff number	8419 8998
Country of origin	Federal Republic of Germany
WEEE-RegNo.	DE 66812464
Dimensions approx incl. carton	B x H x T: 730 x 950 x 670 mm
Net weight	approx. 52 kg
Gross weight carton	approx. 71 kg

Standard units are safety-approved and bear the test marks

